



## Overview

Lead time	Usually in Stock
-----------	------------------

## Main

Main Input Voltage	120 V
Plug standard	NEMA 5-15P
Cable length	6 ft (1.83 m)
Number of cables	1
Provided equipment	User Manual

## Physical

Color	Beige
Height	2.01 in (5.1 cm)
Width	4.25 in (10.8 cm)
Depth	10.51 in (26.7 cm)
Net Weight	2.01 lb(US) (0.91 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

## Input

Maximum Line Current per phase	15 A
Input Frequency	50/60 Hz +/- 5 Hz auto-sensing

## Output

Number of power socket outlets	7
Outlet standard	NEMA 5-15R

## Conformance

UL 1449 TVSS Rating	330
Product Certifications	CSA
Standards	UL 1283 UL 1363 UL 1449
Equipment protection policy	Lifetime : \$100000

## Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

## Surge Protection and Filtering

EP Joule Rating	3420 J
NM Surge Response Time (ns)	0 ns common mode
Common mode rejection	70 dB
Peak current	26 KA common mode 13 kA normal mode
Surge energy rating	1680 J

## Ordering and shipping details

GTIN	731304000204
Package weight(Lbs)	2.31 lb(US) (1.05 kg)

## Packing Units

Package 1 Height	2.09 in (5.3 cm)
Package 1 width	7.24 in (18.4 cm)
Package 1 Length	12.76 in (32.4 cm)
SCC14	10731304000201
Number of Units in Package 2	12
Package 2 Weight	30 lb(US) (13.61 kg)
Number of Units in Package 3	384

## Contractual warranty

Warranty	Limited Lifetime
----------	------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[NET7](#)