



Commercial status

End-of-Sale Notice : MAR 16, 2021

⚠ End-of-Sale Notice

Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	User manual Cord management straps
--------------------	---------------------------------------

Physical

Cable length	1.83 M
Colour	Beige
Depth	14.6 Cm
Height	4.4 Cm
Product weight	0.86 Kg
Width	20.3 Cm

Input

Maximum line current	15 A
Network frequency	50/60 Hz +/- 5 Hz auto-sensing
Plug standard	NEMA 5-15P
Input voltage	120 V

Output

Number of power socket outlets	8
Outlet standard	NEMA 5-15R

Conformance

UL 1449 TVSS rating	330
Product certifications	CSA
Standards	UL 1283 UL 1363 UL 1449
Equipment protection policy	Lifetime : \$100000

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...15240.00 M

Surge Protection and Filtering

EP joule rating	3420 J
Response time	0 ns common mode
Common mode rejection	70 DB
Peak current	26 KA common mode 13 KA normal mode
Surge energy rate	1120 J

Packing Units

Package 1 Weight	1 Kg
Package 1 Height	5.1 Cm
Package 1 width	31.8 Cm
Package 1 Length	15.9 Cm
SCC14	10731304000843
Number of Units in Package 2	12
Package 2 Weight	13.38 Kg
Number of Units in Package 3	240

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: 1,3-Butadiene, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Contractual warranty

Warranty	Limited Lifetime
----------	------------------

Product Life Status :	End of commercialisation
-----------------------	--------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[NET8](#)