



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch lever
Device short name	ZCKY
Product compatibility	XCKL XCKM XCKS XCKJ
Associated head	ZCKD05 ZCKE05
Movement of operating head	Rotary
Type of operator	Roller lever spring return metal variable length)
Type of approach	Lateral approach

Complementary

Switch actuation	By 30° cam
Positive opening	Without

Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C) standard environment -40...158 °F (-40...70 °C) low temperature 50...248 °F (10...120 °C) high temperature
Ambient air temperature for storage	-40...158 °F (-40...70 °C) standard environment -40...158 °F (-40...70 °C) low temperature 50...248 °F (10...120 °C) high temperature
Environmental characteristic	High temperature Low temperature Corrosive

Ordering and shipping details

Category	22411-LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	00785901962571
Package weight(Lbs)	0.07 lb(US) (0.030 kg)
Returnability	Yes
Country of origin	FR

Packing Units

Package 1 Height	0.100 dm
Package 1 width	0.250 dm
Package 1 Length	3.100 dm

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ZCKY439057](#)