

# P11VNT3

APC Performance SurgeArrest 11 Outlet with  
Phone (Splitter), Coax and Ethernet Protection,  
120V



## Overview

Lead time	Usually in Stock
-----------	------------------

## General

Provided equipment	6 ft network cable Coaxial cable Cord management straps Telephone cable User manual
--------------------	---

## Physical

Cable length	8 Ft (2.44 m)
Color	Black
Depth	11.89 In (30.2 cm)
Height	1.57 In (4 cm)
Product Weight	2.34 Lb(US) (1.06 kg)
Width	4.69 In (11.9 cm)

## Input

Input Frequency	50/60 Hz
Plug standard	NEMA 5-15P
Switching current capacity	15 A
Nominal Input Voltage	120 V

## Output

Number of power socket outlets	11
Outlet standard	NEMA 5-15R

## Conformance

UL 1449 TVSS Rating	L-N: 400 L-G: 500 N-G: 500
Product Certifications	CSA NOM
Standards	UL 1363 UL 1449
Equipment protection policy	Lifetime : \$100000

## Environmental

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 Ft (0.00...15240.00 m)

## Surge Protection and Filtering

NM Surge Response Time (ns)	0 ns common mode
Common mode rejection	70 DB
Surge energy rating	3020 J
Data line protection	Analog phone line for phone/fax/modem/DSL (RJ11 connector) Network line - 10/100 Base-T Ethernet (RJ45 connector) Coaxial cable for CATV/SATV/modem/Audio-Video (coax connector)






## Ordering and shipping details

GTIN	00731304249023
Package weight(Lbs)	2.98 Lb(US) (1.35 kg)

## Packing Units

Package 1 Height	2.36 In (6 cm)
Package 1 width	7.56 In (19.2 cm)
Package 1 Length	13.58 In (34.5 cm)
SCC14	10731304249020
Number of Units in Package 2	6
Package 2 Weight	19.58 Lb(US) (8.88 kg)
Package 2 Height	15 In (381.00 mm)
Package 2 width	8 In (203.20 mm)
Package 2 Length	15 In (381.00 mm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	Lifetime
----------	----------

Product Life Status :	Commercialised
-----------------------	----------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[P11VNT3](#)