



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	User Manual
--------------------	-------------

Physical

Color	Black
Depth	2.72 in (6.9 cm)
Height	1.73 in (4.4 cm)
Net Weight	0.40 lb(US) (0.18 kg)
Width	0.75 in (1.9 cm)

Output

Number of power socket outlets	1
--------------------------------	---

Environmental

Ambient air temperature for operation	23...113 °F (-5...45 °C)
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	23...113 °F (-5...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...10000 ft (0.00...3048.00 m)

Surge Protection and Filtering

Data Lines Protected (multi-line only)	1-8
NM Surge Response Time (ns)	1 ns common mode
Peak current	0.25 kA common mode 0.2 kA normal mode

Ordering and shipping details

GTIN	00731304203384
Package weight(Lbs)	0.90 lb(US) (0.41 kg)

Packing Units

Package 1 Height	3.90 in (9.9 cm)
Package 1 width	1.30 in (3.3 cm)
Package 1 Length	3.74 in (9.5 cm)
SCC14	30731304203385
Number of Units in Package 2	96
Package 2 Weight	13.67 lb(US) (6.20 kg)
Package 2 Height	8.125 in (206.38 mm)
Package 2 width	16.25 in (412.75 mm)
Package 2 Length	25.125 in (638.18 mm)
Number of Units in Package 3	28

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	Lifetime
----------	----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[P232R](#)