



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	120 V
Plug standard	NEMA 5-15P
Cable length	6 ft (1.83 m)
Number of cables	1
Provided equipment	User Manual

Physical

Color	White
Height	1.42 in (3.6 cm)
Width	5.20 in (13.22 cm)
Depth	5.20 in (13.22 cm)
Net Weight	1.08 lb(US) (0.49 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input power	1440 W
Input Frequency	60 Hz
Switching current capacity	12 A

Output

Number of power socket outlets	3
Outlet standard	NEMA 5-15R

Conformance

Product Certifications	CUL Listed
Standards	UL 60950-1
Equipment protection policy	Lifetime : \$50000

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Surge Protection and Filtering

NM Surge Response Time (ns)	1 ns common mode
Common mode rejection	40 dB
Surge energy rating	1080 J

Ordering and shipping details

GTIN	731304315193
Package weight(Lbs)	1.17 lb(US) (0.53 kg)

Packing Units

Package 1 Height	2.95 in (7.5 cm)
Package 1 width	5.39 in (13.7 cm)
Package 1 Length	6.10 in (15.5 cm)
SCC14	10731304315190
Number of Units in Package 2	10
Package 2 Weight	13.64 lb(US) (6.19 kg)
Package 2 Height	6.87 in (174.50 mm)
Package 2 width	11.25 in (285.75 mm)
Package 2 Length	15.75 in (400.05 mm)
Number of Units in Package 3	80

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: 1,3-Butadiene, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	Limited Lifetime
----------	------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[P3U3](#)