

P4GC

APC Power-Saving Timer Essential SurgeArrest, 4 Outlet Wall Tap, 120V



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	120 V
Plug standard	NEMA 5-15P
Provided equipment	User Manual

Physical

Color	White
Height	6.50 in (16.5 cm)
Width	3.70 in (9.4 cm)
Depth	2.01 in (5.1 cm)
Net Weight	0.55 lb(US) (0.25 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input Frequency	50/60 Hz
Maximum Input Current per Phase	15 A

Output

Number of power socket outlets	4
Outlet standard	NEMA 5-15R

Conformance

UL 1449 TVSS Rating	400
Product Certifications	ETL
Standards	UL 1449
Equipment protection policy	Lifetime : \$50000

Environmental

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	23...113 °F (-5...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Surge Protection and Filtering

NM Surge Response Time (ns)	1 ns common mode
Common mode rejection	40 dB
Peak current	72 kA common mode
Surge energy rating	1080 J

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304269267
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	PH

Packing Units

Package 1 Height	9.65 in (24.5 cm)
Package 1 width	8.90 in (22.6 cm)
Package 1 Length	2.64 in (6.7 cm)
SCC14	10731304269264
Number of Units in Package 2	6
Package 2 Weight	7.88 lb(US) (3.57 kg)
Package 2 Height	11.68 in (296.67 mm)
Package 2 width	12.13 in (308.10 mm)
Package 2 Length	19.85 in (504.19 mm)
Number of Units in Package 3	288

Contractual warranty

Warranty	Limited Lifetime
----------	------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[P4GC](#)