



Commercial status
End-of-Sale Notice :

⚠ End-of-Sale Notice

Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	User manual
--------------------	-------------

Physical

Colour	Silver
Cable length	1.83 M
Depth	3.8 Cm
Height	29.2 Cm
Product weight	0.45 Kg
Width	5.7 Cm

Input

Network frequency	50/60 Hz +/- 5 Hz auto-sensing
Input voltage	120 V
Maximum line current	15 A
Plug standard	NEMA 5-15P

Output

Number of power socket outlets	6
Outlet standard	NEMA 5-15R

Conformance

Product certifications	CSA
Standards	UL 1449
Equipment protection policy	Lifetime : \$25000
UL 1449 TVSS rating	330

Environmental

Ambient air temperature for operation	0...40 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 %
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 M
Storage Relative Humidity	0...95 %

Surge Protection and Filtering

EP joule rating	1080 J
Let through voltage rating	330 V
Response time	0 ns common mode
Common mode rejection	20 DB
Peak current	20 KA common mode 10 KA normal mode
Surge energy rate	490 J

Packing Units

Package 1 Weight	0.6 Kg
Package 1 Height	33.8 Cm
Package 1 width	14.7 Cm
Package 1 Length	3.8 Cm
SCC14	10731304222498
Number of Units in Package 2	12
Package 2 Weight	2.72 Kg
Package 2 Height	368.30 Mm
Package 2 width	165.10 Mm
Package 2 Length	158.75 Mm

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	Lifetime
----------	----------

Product Life Status : **End of commercialisation**

P6BMP4 may be replaced by any of the following products:



P6B

APC Essential SurgeArrest, 6 outlet

Qty 1

Substitution date: | Migration SPD

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[P6BMP4](#)