



## Overview

Lead time	Usually in Stock
-----------	------------------

## Main

Main Input Voltage	120 V
Plug standard	NEMA 5-15P
Provided equipment	User Manual USB Power Adapter

## Physical

Color	Beige
Height	4.02 in (10.2 cm)
Width	1.50 in (3.8 cm)
Depth	5.51 in (14 cm)
Net Weight	0.55 lb(US) (0.25 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

## Input

Input power	1200 W
Maximum Line Current per phase	15 A
Input Frequency	50/60 Hz +/- 5 Hz auto-sensing
Maximum Input Current per Phase	15 A
Switching current capacity	15 A

## Output

Number of power socket outlets	6
Outlet standard	NEMA 5-15R

## Conformance

UL 1449 TVSS Rating	400
Product Certifications	ETL
Equipment protection policy	Lifetime : \$50000

## Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

## Surge Protection and Filtering

NM Surge Response Time (ns)	1 ns common mode
Common mode rejection	40 dB
Peak current	72 KA common mode 60 kA per phase normal mode
Surge energy rating	1080 J

## Ordering and shipping details

GTIN	731304331827
Package weight(Lbs)	0.57 lb(US) (0.26 kg)

## Packing Units

Package 1 Height	9.49 in (24.1 cm)
Package 1 width	2.24 in (5.7 cm)
Package 1 Length	7.76 in (19.7 cm)
SCC14	10731304331824
Number of Units in Package 2	6
Package 2 Weight	5 lb(US) (2.27 kg)
Package 2 Height	10 in (254.00 mm)
Package 2 width	8.4 in (213.36 mm)
Package 2 Length	13.4 in (340.36 mm)
Number of Units in Package 3	504

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: 1,3-Butadiene, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Lead free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	Limited Lifetime
----------	------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[P6WU2](#)