

# Product data sheet

## Characteristics

# P7T10

APC Essential SurgeArrest, 7 outlet, phone line protection, 10 ft power cord



## Overview

Lead time	Usually in Stock
-----------	------------------

## General

Provided equipment	2 x 1.8 Meter Tel cable User manual
--------------------	--

## Physical

Cable length	10 Ft (3.05 m)
Color	Beige
Depth	2.01 In (5.1 cm)
Height	14.02 In (35.6 cm)
Product Weight	1.23 Lb(US) (0.56 kg)
Width	2.99 In (7.6 cm)

## Input

Maximum Line Current per phase	15 A
Input Frequency	50/60 Hz +/- 5 Hz manual switch
Plug standard	NEMA 5-15P
Nominal Input Voltage	120 V

## Output

Number of power socket outlets	7
Outlet standard	NEMA 5-15R

## Conformance

UL 1449 TVSS Rating	330
Product Certifications	CSA
Standards	UL 1449
Equipment protection policy	Lifetime : \$25000

## Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 Ft (0.00...15240.00 m)

## Surge Protection and Filtering

NM Surge Response Time (ns)	0 ns common mode
Common mode rejection	55 DB
Peak current	30 KA common mode 10 KA normal mode
Surge energy rating	840 J
Data line protection	RJ11 Modem/Fax/DSL protection (two wire single line)

## Ordering and shipping details

GTIN	00731304016588
Package weight(Lbs)	1.81 Lb(US) (0.82 kg)

## Packing Units

Package 1 Height	14.02 In (35.6 cm)
Package 1 width	5.24 In (13.3 cm)
Package 1 Length	1.89 In (4.8 cm)
SCC14	10731304016585
Number of Units in Package 2	12
Package 2 Weight	20 Lb(US) (9.07 kg)
Package 2 Height	8.13 In (206.50 mm)
Package 2 width	15.5 In (393.70 mm)
Package 2 Length	16.37 In (415.80 mm)
Number of Units in Package 3	360

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: 1,3-Butadiene, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	Limited Lifetime
----------	------------------

Product Life Status : **Commercialised**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[P7T10](#)