



Commercial status

End-of-Sale Notice : JUL 08, 2021

⚠ End-of-Sale Notice

Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	Coaxial cable Network cable Telephone cable User manual
--------------------	--

Physical

Colour	Black
Cable length	1.83 M
Depth	5.1 Cm
Height	39.4 Cm
Product weight	0.95 Kg
Width	9.5 Cm

Input

Network frequency	50/60 Hz +/- 5 Hz auto-sensing
Input voltage	120 V
Maximum line current	15 A
Plug standard	NEMA 5-15P

Output

Number of power socket outlets	8
Outlet standard	NEMA 5-15R

Conformance

Product certifications	CSA
Equipment protection policy	Lifetime : \$100000
UL 1449 TVSS rating	330

Environmental

Ambient air temperature for operation	0...40 °C
Operating altitude	0...50000 ft
Relative humidity	0...95 %
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 M
Storage Relative Humidity	0...95 %

Surge Protection and Filtering

Data line protection	RJ11 modem/fax/DSL protection (four wire dual line) RJ45 10/100 Base-T Ethernet protection Cable modem/video protection
Let through voltage rating	330 V
Data line protected	1-4
Response time	0 ns common mode
Common mode rejection	70 DB
Peak current	40 KA common mode 20 KA normal mode
Surge energy rate	4720 J

Packing Units

Package 1 Weight	1.23 Kg
Package 1 Height	45 Cm
Package 1 width	18 Cm
Package 1 Length	6 Cm
SCC14	10731304260155
Number of Units in Package 2	12
Package 2 Weight	15.42 Kg
Package 2 Height	609.60 Mm
Package 2 width	279.40 Mm
Package 2 Length	508.00 Mm
Number of Units in Package 3	384

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
California proposition 65	WARNING: This product can expose you to chemicals including: 1,3-Butadiene, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Contractual warranty

Warranty	Lifetime
----------	----------

Product Life Status : **End of commercialisation**

P8VNTG may be replaced by any of the following products:



P11VNT3

APC Performance SurgeArrest 11 Outlet with Phone (Splitter), Coax and Ethernet Protection, 120V

Qty 1

Substitution date: |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[P8VNTG](#)