



### Main

Product or Component Type	Cross
Range of Product	Powerbus

### Complementary

Current Rating	100 A
Busbar Configuration	4A L1 + L2 + N + L3
Busbar Material	Silver plated copper busbar
Integral Ground	50 percent capacity integral ground bus
Voltage Rating	600 V AC
Number of Phases	3 phase
Wiring configuration	4-wire (100 percent neutral)
Enclosure material	Painted aluminium Black

### Environment

IP Degree of Protection	IP40
-------------------------	------




### Ordering and shipping details

Category	20171-100A & 225A BUSWAY LENGTHS & FITTINGS
Discount Schedule	PE8
Returnability	Yes

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	24.00 lb(US) (10.886 kg)

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[PBCF4A100ACRB](#)