



Main

Product or Component Type	Tap box
Range of Product	Powerbus
Options	PM5350 meter

Complementary

Current Rating	225 A
Busbar Configuration	4A L1 + L2 + N + L3
Busbar Material	Silver plated copper busbar
Integral Ground	50 percent capacity integral ground bus
Voltage Rating	208Y/120 V AC
Number of Phases	3 phase
Wiring configuration	4-wire (100 percent neutral)
Wire Gauge	AWG 10...AWG 2/0 1 ground AWG 6...300 kcmil 1 phase and neutral
Enclosure material	Painted aluminium Black

Environment

IP Degree of Protection	IP40
-------------------------	------

Ordering and shipping details

Category	20171-100A & 225A BUSWAY LENGTHS & FITTINGS
Discount Schedule	PE8
Returnability	No

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	46.00 lb(US) (20.865 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes

China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[PBCF4A225ATBM1B](#)