



### Overview

Lead time	Usually Ships within 8 Weeks
-----------	------------------------------

### Main

Main Input Voltage	120 V
Plug standard	NEMA 5-15P
Cable length	15 ft (4.57 m)
Number of cables	1
Provided equipment	User Manual

### Physical

Color	Yellow
Height	13.50 in (34.3 cm)
Width	4.76 in (12.1 cm)
Depth	1.73 in (4.4 cm)
Net Weight	2.43 lb(US) (1.1 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

### Input

Maximum Line Current per phase	15 A
Input Frequency	50/60 Hz +/- 5 Hz auto-sensing

### Output

Number of power socket outlets	8
Outlet standard	NEMA 5-15R

### Conformance

UL 1449 TVSS Rating	330
Product Certifications	CSA
Standards	UL 1449
Equipment protection policy	Lifetime : \$5000

## Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

## Surge Protection and Filtering

EP Joule Rating	820 J
NM Surge Response Time (ns)	0 ns common mode
Surge energy rating	800 J

## Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304238331
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	PH

## Packing Units

Package 1 Height	13.50 in (34.3 cm)
Package 1 width	4.76 in (12.1 cm)
Package 1 Length	2.91 in (7.4 cm)
SCC14	10731304238338
Number of Units in Package 2	12
Package 2 Weight	32.78 lb(US) (14.87 kg)
Package 2 Height	8 in (203.20 mm)
Package 2 width	15 in (381.00 mm)
Package 2 Length	29 in (736.60 mm)
Number of Units in Package 3	180

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: 1,3-Butadiene, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	Limited Lifetime
----------	------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[PDIY8](#)