

Main

Device short name	L100
Series name	Severe duty

Complementary

Line Rated Current	20 A
AWG gauge	AWG 12 1 AWG 14 2
Body material	Cast aluminium
Contact code designation	A600 P600
Contact operation	Double-break isolated
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Function available	Two circuit - single operation
Material	Metal front cover
Mounting support	panel
Switch function	2-pole switch
Torque value	190 ozf.in
Connector type	4 pins male

Environment

Ambient air temperature for operation	0...200 °F (-18...93 °C)
NEMA degree of protection	NEMA 1/4/13
Product certifications	CSA LR25490 class 3211 03 UL listed file E42259 CCN NKCR CE
Vibration resistance	30 gn 10...55 Hz)

Ordering and shipping details

Category	22426 - LIMIT SWITCHES,TYPE L
Discount Schedule	DS1
GTIN	00785901171812
Nbr. of units in pkg.	1
Package weight(Lbs)	1.5 lb(US) (0.68 kg)
Returnability	No
Country of origin	MX

Packing Units

Package 1 Height	2.54 in (6.452 cm)
Package 1 width	1.00 in (2.540 cm)
Package 1 Length	6.45 in (16.387 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[PL100WS2M2](#)