

Product data sheet

Characteristics

PTEL2

APC ProtectNet standalone surge protector for analog/DSL phone lines (2 lines, 4 wires)



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	User manual
--------------------	-------------

Physical

Color	Beige
Depth	1.10 In (2.8 cm)
Height	4.06 In (10.3 cm)
Product Weight	0.13 Lb(US) (0.06 kg)
Width	1.85 In (4.7 cm)

Output

Number of power socket outlets	0
--------------------------------	---

Conformance

Product Certifications	UL Listed
Standards	UL 497A

Environmental

Ambient Air Temperature for Operation	5...113 °F (-15...45 °C)
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %

Surge Protection and Filtering

Data Lines Protected (multi-line only)	3-6 RJ45
NM Surge Response Time (ns)	1 ns common mode
Peak current	0.15 KA common mode 0.2 KA normal mode
Data line protection	RJ45 Modem/Fax/DSL protection (four wire dual line)

Ordering and shipping details

GTIN	00731304000433
Package weight(Lbs)	0.31 Lb(US) (0.14 kg)

Packing Units

Package 1 Height	4.09 In (10.4 cm)
Package 1 width	3.54 In (9 cm)
Package 1 Length	1.14 In (2.9 cm)
SCC14	10731304000430
Number of Units in Package 2	144
Package 2 Weight	18 Lb(US) (8.16 kg)
Number of Units in Package 3	750

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	10 years repair or replace
----------	----------------------------

Product Life Status : Commercialised

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[PTEL2](#)