



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Number of cables	1
Battery Type	Lead-Acid battery
Provided Equipment	All required connectors Battery recycling guide Reusable packaging Installation guide

Physical

Color	Black
Height	2.60 in (6.6 cm)
Width	2.64 in (6.7 cm)
Depth	5.28 in (13.4 cm)
Net Weight	3.09 lb(US) (1.4 kg)
Mounting Mode	Not rack-mountable

Output

Battery Capacity	3 Ah
------------------	------

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

Batteries & Runtime

Battery Slots Empty	0
Included Battery Modules	0
Battery Voltage	12 V
RBC Quantity	1

Ordering and shipping details

GTIN	731304220930
Package weight(Lbs)	3.68 lb(US) (1.67 kg)

Packing Units

Package 1 Height	3.70 in (9.4 cm)
Package 1 width	5.75 in (14.6 cm)
Package 1 Length	7.36 in (18.7 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[RBC47](#)