

# RBC9

## APC Replacement Battery Cartridge #9 with 2 Year Warranty



### Overview

Lead time	Usually in Stock
-----------	------------------

### General

Provided Equipment	All required connectors Battery recycling guide Reusable packaging Installation guide
--------------------	--

### Physical

Color	Black
Depth	5.91 In (15 cm)
Height	3.70 In (9.4 cm)
Product Weight	10.91 Lb(US) (4.95 kg)
Width	5.12 In (13 cm)

### Output

Battery Capacity	7.0 Ah
------------------	--------

### Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 Ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

Batteries & Runtime

Battery Slots Empty	0
Included Battery Modules	0
Battery Voltage	24 V
Battery Type	Lead-Acid battery
RBC Quantity	1

Ordering and shipping details

GTIN	00731304003311
Package weight(Lbs)	12.02 Lb(US) (5.45 kg)

Packing Units

Package 1 Height	6.61 In (16.8 cm)
Package 1 width	6.61 In (16.8 cm)
Package 1 Length	8.82 In (22.4 cm)
Number of Units in Package 3	100

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Product Life Status :	Commercialised
-----------------------	----------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[RBC9](#)