

Complementary

Line Rated Current	320 A
Depth	18.38 in (466.85 mm)
Electrical Connection	Screw clamp terminal
Height	24 in (609.60 mm)
Permissible voltage	600 V AC
Net Weight	187 lb(US) (84.82 kg)
Protection Type	Harmonic distortion Overvoltage protection Current protection
Width	16.88 in (428.75 mm)

Environment

Product Certifications	CSA LR29753 CE UL listed file E180243
------------------------	---

Ordering and shipping details

Category	22062-LINE REACTORS/FILTERS (RL,KLC)
Discount Schedule	CP4C
GTIN	785901142867
Nbr. of units in pkg.	1
Package weight(Lbs)	236.00 lb(US) (107.048 kg)
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	24.02 in (61 cm)
Package 1 width	16.89 in (42.9 cm)
Package 1 Length	18.39 in (46.7 cm)

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[RL32013](#)