

Complementary

Line Rated Current	500 A
Depth	24.9 in (632.46 mm)
Electrical Connection	Screw clamp terminal
Height	47 in (1193.80 mm)
Permissible voltage	600 V AC
Net Weight	354 lb(US) (160.57 kg)
Protection Type	Harmonic distortion Overvoltage protection Current protection
Width	26.55 in (674.37 mm)

Environment

Product Certifications	CE UL listed file E180243 CSA LR29753
------------------------	---

Ordering and shipping details

Category	22062-LINE REACTORS/FILTERS (RL,KLC)
Discount Schedule	CP4C
GTIN	785901142911
Nbr. of units in pkg.	1
Package weight(Lbs)	336.00 lb(US) (152.407 kg)
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	47.01 in (119.4 cm)
Package 1 width	26.54 in (67.4 cm)
Package 1 Length	24.88 in (63.2 cm)

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[RL50013](#)