

SBP10KRMT4U

APC Service Bypass Panel- 200/208/240V;
100A; MBB; Hardwire input; (3) L6-30R (3)
L6-20R output



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	200 V 208 V
Main Output Voltage	200 V 208 V
Other Output Voltage	240 V
Number of rack unit	4U
Provided Equipment	Installation guide Rack Mounting brackets User Manual

Physical

Color	Black
Height	7.01 in (17.8 cm)
Width	17.01 in (43.2 cm)
Depth	26.50 in (67.3 cm)
Net Weight	48.10 lb(US) (21.8181818181818 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted

Input

Input Frequency	50/60 Hz
Number of input connectors	1 Hard Wire 3-wire (2PH + G)
Acceptable Input Voltage	200...240 V
Max line current	100 A
Input current limits	100 A
Load Capacity	20000 VA
Load Power Factor Range	0...1

Output

Maximum Total Current Draw per Phase	100 A
Number of power socket outlets	3 NEMA L6-20R 3 NEMA L6-30R
Protection Type	Circuit breaker
Efficiency	99 %

Conformance

Product Certifications	CSA GOST
Standards	EN 60950 IEC 60950 IEC 60950 UL 1778

Environmental

Ambient Air Temperature for Operation	-4...122 °F (-20...50 °C)
Relative Humidity	0...95 %
Operating altitude	0...15000 ft
Ambient Air Temperature for Storage	-40...149 °F (-40...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304212621
Package weight(Lbs)	70.15 lb(US) (31.8181818181818 kg)

Packing Units

Package 1 Height	12.01 in (30.5 cm)
Package 1 width	24.02 in (61 cm)
Package 1 Length	39.02 in (99.1 cm)
Number of Units in Package 3	6

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

Contractual warranty

Warranty	2 years (parts only)
----------	----------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SBP10KRMT4U](#)