

SBP5000RMT2U

APC Service Bypass Panel - 200/208/240V;
30A; BBM; L6-30P input; (2) L6-30R (2)
L6-20R output



Overview

Lead time	Usually in Stock
-----------	------------------



Main

Main Input Voltage	200 V 208 V
Main Output Voltage	200 V 208 V
Other Output Voltage	240 V
Plug standard	NEMA L6-30P
Number of rack unit	2U
Cable length	10 ft (3.05 m)
Number of cables	1
Provided Equipment	Installation guide Rack Mounting brackets User Manual

Physical

Color	Black
Height	3.50 in (8.9 cm)
Width	17.01 in (43.2 cm)
Depth	25.98 in (66 cm)
Net Weight	30.07 lb(US) (13.64 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted

Input

Input Frequency	50/60 Hz
Max line current	24 A
Input current limits	24 A
Load Capacity	5000 VA
Load Power Factor Range	0...1

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Output

Maximum Total Current Draw per Phase	24 A
Number of power socket outlets	2 NEMA L6-20R 2 NEMA L6-30R
Protection Type	Circuit breaker
Efficiency	99 %

Conformance

Product Certifications	CSA GOST
Standards	EN 60950 IEC 60950 IEC 60950 UL 1778

Environmental

Ambient Air Temperature for Operation	-4...122 °F (-20...50 °C)
Relative Humidity	0...95 %
Operating altitude	0...15000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304212584
Package weight(Lbs)	54.10 lb(US) (24.54 kg)

Packing Units

Package 1 Height	7.99 in (20.3 cm)
Package 1 width	24.02 in (61 cm)
Package 1 Length	39.02 in (99.1 cm)
Number of Units in Package 3	10

Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
-------------------	---

Contractual warranty

Warranty	2 years (parts only)
----------	----------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SBP5000RMT2U](#)