



Overview

| | |
|--------------|--|
| Presentation | APC Smart-UPS SC is ideal for small and medium businesses looking to protect networking equipment and point-of-sale (POS) devices from power disturbances and outages. The Smart-UPS SC features network grade protection, hot swap batteries, and built-in data line protection for worry free uninterruptible power protection for increased availability. Built on the same standards as the award-winning Smart-UPS, Smart-UPS SC provides the basic features and manageability needed to protect entry-level applications |
| Lead time | Usually in Stock |

Main

| | |
|----------------------------|--|
| Main Input Voltage | 120 V |
| Main Output Voltage | 120 V |
| Rated power in W | 390 W |
| Rated power in VA | 620 VA |
| Plug standard | NEMA 5-15P |
| Nb of power socket outlets | 4 NEMA 5-15R |
| Cable length | 6 ft (1.83 m) |
| Number of cables | 1 |
| Battery type | Lead-Acid battery |
| Provided equipment | User Manual Smart UPS signalling RS-232 cable CD with software |

General

| | |
|-------------------------------------|-------------|
| Number of power module filled slots | 0 |
| Number of power module free slots | 0 |
| Product web sub-family | Entry level |
| Redundant | No |

Physical

| | |
|---------------------|-------------------------|
| Color | Gray |
| Height | 6.61 in (16.8 cm) |
| Width | 4.69 in (11.9 cm) |
| Depth | 14.49 in (36.8 cm) |
| Net Weight | 27.07 lb(US) (12.28 kg) |
| Mounting Location | Front |
| Mounting preference | No preference |
| Mounting Mode | Not rack-mountable |
| Two post mountable | 0 |
| USB compatible | No |

Input

| | |
|-------------------------|-------------------------------------|
| Efficiency at full load | 75...154 V adjustable 82...144 V |
| Input Frequency | 50/60 Hz +/- 3 Hz auto-sensing |

Output

| | |
|----------------------------------|-------------------------------------|
| Maximum configurable power in VA | 620 VA |
| Max Configurable Power (Watts) | 390 W |
| Transfer Time | 4ms typical : 8ms maximum |
| Topology | Line Interactive |
| Waveform Type | Stepped approximation to a sinewave |
| Output Frequency (sync to mains) | 50/60 Hz +/- 3 Hz sync to mains |

Conformance

| | |
|-----------------------------|--------------------------------|
| Product certifications | CSA |
| Equipment protection policy | Lifetime : \$150000 |
| Standards | FCC Part 15 class A UL 1778 |

Environmental

| | |
|---------------------------------------|----------------------------------|
| Acoustic level | 45 dBA |
| Heat dissipation | 70 Btu/h |
| Operating altitude | 0...10000 ft |
| Ambient Air Temperature for Operation | 32...104 °F (0...40 °C) |
| Ambient Air Temperature for Storage | 5...113 °F (-15...45 °C) |
| Storage altitude | 0...50000 ft (0.00...15240.00 m) |
| Relative Humidity | 0...95 % |
| Storage Relative Humidity | 0...95 % |

Batteries & Runtime

| | |
|------------------------------|-----------------|
| Battery Voltage | 12 V |
| Extendable Run Time | 0 |
| Battery capacity | 12.0 Ah |
| Included Battery Modules | 0 |
| Battery Slots Empty | 0 |
| Typical recharge time | 5 h |
| RBC Quantity | 1 |
| Battery life | 3...5 year(s) |
| Battery power in VAh | 132 VAh runtime |
| Battery Charge Power (Watts) | 26 W rated |

Communications & Management

| | |
|---------------------------|--|
| Audible Alarm | Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm |
| Control panel | LED status display with On Line : On Battery : Replace Battery and Overload indicators |
| Emergency Power Off (EPO) | Optional |
| Free slots | 0 |

Surge Protection and Filtering

| | |
|----------------------|--|
| Data line protection | RJ45 Modem/Fax/DSL/10-100 Base-T protection |
| Surge energy rating | 412 J |
| Filtering | Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m |

Ordering and shipping details

| | |
|-----------------------|-----------------------------|
| Category | 11309 - APC RESALE PRODUCTS |
| GTIN | 731304222620 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 1 lb(US) (0.45 kg) |
| Returnability | No |
| Country of origin | PH |

Packing Units

| | |
|------------------------------|--------------------|
| Package 1 Height | 12.52 in (31.8 cm) |
| Package 1 width | 10.31 in (26.2 cm) |
| Package 1 Length | 20.00 in (50.8 cm) |
| Number of Units in Package 3 | 12 |

Offer Sustainability

| | |
|-----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |
| Optimized Energy Efficiency | Energy efficient product |
| Take-back | Take-back program available |

Contractual warranty

| | |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SC620](#)