

# SMT1500R2X122

APC Smart-UPS, Line Interactive, 1500VA,  
Rackmount 2U, 120V, 6x NEMA 5-15R outlets,  
SmartSlot, AVR, LCD, W/L5-15P



## Overview

Lead time	Usually Ships within 2 Weeks
-----------	------------------------------



## Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Kw Rating	1000 W
Rated power in VA	1440 VA
Input Connection Type	NEMA L5-15P
Nb of power socket outlets	6 NEMA 5-15R
Number of rack unit	2U
Cable length	8 ft (2.44 m)
Number of cables	1
Battery Type	Lead-Acid battery
Provided equipment	CD with software Documentation CD Installation guide Rack Mounting support rails Smart UPS signalling RS-232 cable USB cable

## General

Number of power module filled slots	0
Number of power module free slots	0
Redundant	No
Variant option	Twist-lock L5-15P Input Plug

## Physical

Color	Black
Height	3.50 in (8.9 cm)
Width	17.01 in (43.2 cm)
Depth	17.99 in (45.7 cm)
Net Weight	63.14 lb(US) (28.64 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted

Two post mountable	0
USB compatible	Yes

## Input

Efficiency at full load	75...154 V adjustable 82...144 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

## Output

Harmonic distortion	Less than 5%
Maximum configurable power in VA	1440 VA
Max Configurable Power (Watts)	1000 W
Transfer Time	4ms typical : 8ms maximum
Topology	Line Interactive
Waveform Type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

## Conformance

Product Certifications	CSA
Equipment protection policy	Lifetime : \$150000
Standards	FCC Part 15 class A UL 1778

## Environmental

Acoustic level	46 dBA
Heat dissipation	90 Btu/h
Operating altitude	0...10000 ft
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

## Batteries & Runtime

Extendable Run Time	0
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery Life	4...6 year(s)
Battery power in VAh	432 VAh runtime
Battery Charge Power (Watts)	144 W rated

## Communications & Management

Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Control panel	Multi-function LCD status and control console
Free slots	1

## Surge Protection and Filtering

Surge energy rating	459 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m

## Ordering and shipping details

GTIN	731304294061
Package weight(Lbs)	70.35 lb(US) (31.91 kg)

## Packing Units

Package 1 Height	9.88 in (25.1 cm)
Package 1 width	23.39 in (59.4 cm)
Package 1 Length	23.74 in (60.3 cm)
Number of Units in Package 3	16

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SMT1500R2X122](#)