

# SMT1500X413

APC Smart-UPS 1500VA LCD 120V Audible  
Alarm Disabled (Not for sale in CO, VT or WA)



## Overview

Presentation	Reliable network power protection designed for deployment in retail and open access environments.
Lead time	Usually Ships within 4 Weeks

## General

Provided equipment	CD with software Documentation CD Smart UPS signalling RS-232 cable USB cable
Number of tare power	30 W
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No
Variant option	Audible alarm disabled (can be re-enabled by user)

## Physical

Cable length	6 Ft (1.83 m)
Color	Black
Depth	17.28 In (43.9 cm)
Height	8.62 In (21.9 cm)
Mounting Location	Front
Mounting preference	No preference
Product Weight	53.11 Lb(US) (24.09 kg)
Mounting Mode	Not rack-mountable
Two post mountable	0
USB compatible	Yes
Width	6.73 In (17.1 cm)

## Input

Input Frequency	50/60 Hz +/- 3 Hz auto-sensing
Plug standard	NEMA 5-15P
Efficiency at full load	75...154 V adjustable 82...144 V
Number of cables	1
Nominal Input Voltage	120 V

## Output

Kw Rating	1000 W
Max Configurable Power (Watts)	1000 W
Harmonic distortion	Less than 5%
Output frequency	50/60 Hz +/- 3 Hz sync to mains
Topology	Line Interactive
Waveform Type	Sine wave
Nb of power socket outlets	8 NEMA 5-15R
Output voltage	120 V
Maximum configurable power in VA	1440 VA
Rated power in VA	1440 VA
Transfer Time	4ms typical : 8ms maximum

## Conformance

Product Certifications	CUL Listed
Standards	UL 1778
Equipment protection policy	Lifetime : \$150000

## Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 Ft (0.00...15240.00 m)
Acoustic level	45 dBA
Heat dissipation	135 Btu/H

## Batteries & Runtime

Battery Type	Lead-Acid battery
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 H
RBC Quantity	1
Liquid Electrolyte Value	0
Battery Charge Power (Watts)	136 W rated
Battery power in VAH	408 VAh runtime
Battery life	3...5 Year(S)
Extendable Run Time	0

## Communications & Management

Free slots	1
Control panel	Multi-function LCD status and control console
Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Emergency Power Off (EPO)	Optional

## Surge Protection and Filtering

Surge energy rating	459 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m

## Ordering and shipping details

GTIN	00731304284307
Package weight(Lbs)	60.03 Lb(US) (27.23 kg)

## Packing Units

Package 1 Height	14.80 In (37.6 cm)
Package 1 width	12.91 In (32.8 cm)
Package 1 Length	23.43 In (59.5 cm)
Number of Units in Package 3	24

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---

Product Life Status : **Commercialised**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SMT1500X413](#)