

SMT1500X448

APC Smart-UPS, Line Interactive, 1500VA,
Tower, 120V, 8x NEMA 5-15R outlets,
SmartSlot, AVR, LCD



Overview

Lead time	Usually Ships within 2 Weeks
-----------	------------------------------

Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Rated power in W	1000 W
Rated power in VA	1440 VA
Plug standard	NEMA 5-15P
Nb of power socket outlets	8 NEMA 5-15R
Cable length	6 ft (1.83 m)
Number of cables	1
Battery type	Lead-Acid battery
Provided equipment	CD with software Documentation CD Smart UPS signalling RS-232 cable USB cable Web/SNMP Management Card

General

Number of power module filled slots	0
Number of power module free slots	0
Redundant	No
Variant option	Web/SNMP card AP9631 preinstalled

Physical

Color	Black
Height	8.62 in (21.9 cm)
Width	6.73 in (17.1 cm)
Depth	17.28 in (43.9 cm)
Net Weight	53.11 lb(US) (24.09 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Two post mountable	0
USB compatible	Yes

Input

Efficiency at full load	75...154 V adjustable 82...144 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic distortion	Less than 5%
Maximum configurable power in VA	1440 VA
Max Configurable Power (Watts)	1000 W
Transfer Time	4ms typical : 8ms maximum
Topology	Line Interactive
Waveform Type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product certifications	CUL Listed
Equipment protection policy	Lifetime : \$150000
Standards	UL 1778

Environmental

Acoustic level	45 dBA
Heat dissipation	135 Btu/h
Operating altitude	0...10000 ft
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

Batteries & Runtime

Extendable Run Time	0
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery life	3...5 year(s)
Battery power in VAh	408 VAh runtime
Battery Charge Power (Watts)	136 W rated

Communications & Management

Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Control panel	Multi-function LCD status and control console
Emergency Power Off (EPO)	Optional
Free slots	0
Pre-Installed SmartSlot™ Cards	Network management card 2 with environmental monitoring

Surge Protection and Filtering

Surge energy rating	459 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m






Ordering and shipping details

GTIN	731304284314
Package weight(Lbs)	60.03 lb(US) (27.23 kg)

Packing Units

Package 1 Height	14.80 in (37.6 cm)
Package 1 width	12.91 in (32.8 cm)
Package 1 Length	23.43 in (59.5 cm)
Number of Units in Package 3	24

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SMT1500X448](#)