

SQR42201LA

Socket-outlet, X Series, 20A, standard, duplex, tamper resistant, weatherproof, commercial, light almond, matte finish



Main

Range	Square D X Series
Product or Component Type	Socket-outlet
Device Application	Power supply
Device presentation	Mechanism with fixing frame
Aesthetic name	X Series
Outlet poles configuration	2P + E
Outlet standard	NEMA
Socket additional information	Tamper resistant

Complementary

Body type	Standard
Number of modules	1
Socket number	2
Number of gangs	1 gang
[Ie] rated operational current AC	20 A
[Ue] rated operational voltage	125 V
Network type	AC
Network Frequency	60 Hz
Mounting Mode	By screws
Device mounting	Flush
Material	Plastic strap Metal fixing frame
Color	Light almond
Surface Finish	Matte
Connections - terminals	Phase and neutral 4 screw terminal AWG 12...AWG10) copper Earth 1 screw terminal copper
Earth circuit	Self earthing
Width	1.46 in (37 mm)
Height	4.06 in (103 mm)
Depth	1.06 in (27 mm)
Quantity per Set	1 piece

Environment

Environmental characteristic	Weatherproof
Product Certifications	cULus
Standards	UL 498 NEMA 5-20R

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	09932-WD BASIC DEVICES
Discount Schedule	DE9
GTIN	785901535638
Nbr. of units in pkg.	1
Package weight(Lbs)	3.35 oz (95.0 g)
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.17 in (10.6 cm)
Package 1 width	1.22 in (3.1 cm)
Package 1 Length	1.65 in (4.2 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	2.24 lb(US) (1.017 kg)
Package 2 Height	4.45 in (11.3 cm)
Package 2 width	3.58 in (9.1 cm)
Package 2 Length	6.50 in (16.5 cm)
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Weight	24.61 lb(US) (11.165 kg)
Package 3 Height	7.28 in (18.5 cm)
Package 3 width	9.49 in (24.1 cm)
Package 3 Length	18.90 in (48 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: carbon black, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	2 years
----------	---------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SQR42201LA](#)