



Commercial status

This Product is Obsolete :

⚠ This Product is Obsolete

Overview

Lead time	Usually Ships within 2 Weeks
-----------	------------------------------

General

Provided equipment	CD with software Smart UPS signalling RS-232 cable User manual
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No
Variant option	Installed Accessory

Physical

Cable length	8 Ft (2.44 m)
Number of rack unit	2U
Color	Black
Depth	25.98 In (66 cm)
Height	3.50 In (8.9 cm)
Mounting Location	Front
Mounting preference	Lower
Product Weight	96.21 Lb(US) (43.64 kg)
Mounting Mode	Rack-mounted
USB compatible	Yes
Width	19.02 In (48.3 cm)

Input

Input Frequency	50/60 Hz +/- 3 Hz auto-sensing
Plug standard	NEMA L5-30P
Efficiency at full load	75...154 V adjustable 82...144 V
Number of cables	1
Nominal Input Voltage	120 V

Output

Kw Rating	2700 W
Max Configurable Power (Watts)	2700 W
Harmonic distortion	Less than 5 % at full load
Output frequency	47...53 Hz for 50 Hz nominal sync to mains 57...63 Hz for 60 Hz nominal sync to mains
Topology	Line Interactive
Waveform Type	Sine wave
Nb of power socket outlets	6 NEMA 5-15R 2 NEMA 5-20R
Output voltage	120 V
Maximum configurable power in VA	3000 VA
Rated power in VA	3000 VA

Conformance

Standards	UL 1778
Equipment protection policy	Lifetime : \$150000

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 Ft (0.00...15240.00 m)
Acoustic level	47 dBA
Heat dissipation	400 Btu/H

Batteries & Runtime

Battery Type	Lead-Acid battery
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 H
Liquid Electrolyte Value	0
Battery Charge Power (Watts)	175 W rated
Battery power in VAH	528 VAh runtime
Battery life	3...5 Year(S)
Extendable Run Time	0

Communications & Management

Free slots	0
Control panel	LED status display with load and battery bar-graphs and On Line : On Battery : Replace Battery : and Overload Indicators
Audible Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Emergency Power Off (EPO)	Yes

Surge Protection and Filtering

Surge energy rating	480 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m

Ordering and shipping details

GTIN	00731304222446
Package weight(Lbs)	125.27 Lb(US) (56.82 kg)

Packing Units

Package 1 Height	10.00 In (25.4 cm)
Package 1 width	24.49 In (62.2 cm)
Package 1 Length	38.58 In (98 cm)
Number of Units in Package 3	8

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Product Life Status : **End of commerc. announced**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SUA3000R2X180](#)