



### Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

### General

Provided Equipment	Installation guide User Manual
--------------------	-----------------------------------

### Physical

Cable length	3 ft (0.91 m)
Color	Black
Depth	25.98 in (66 cm)
Height	17.01 in (43.2 cm)
Product Weight	125.27 lb(US) (56.82 kg)
Width	5.12 in (13 cm)

### Input

Permissible voltage	180...264 V
Input current limits	30 A
Load Capacity	4800 VA
Input Frequency	50/60 Hz
Plug standard	NEMA L6-30P
Nominal Input Voltage	208 V 240 V

### Output

Max current draw	30 A
Protection Type	Circuit breaker
Number of power socket outlets	8 NEMA 5-20R 2 NEMA L6-20R 1 NEMA L6-30R 1 NEMA L14-30R
Output voltage	120 V 208 V

## Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)




## Ordering and shipping details

Package weight(Lbs)	140.30 lb(US) (63.64 kg)
---------------------	--------------------------

## Packing Units

Package 1 Height	13.66 in (34.7 cm)
Package 1 width	23.74 in (60.3 cm)
Package 1 Length	38.58 in (98 cm)
SCC14	10731304217807
Number of Units in Package 3	6

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SURT003](#)