



### Overview

Lead time	Usually in Stock
-----------	------------------

### General

Provided equipment	Installation guide
--------------------	--------------------

### Physical

Color	Black
Depth	27.56 in (70 cm)
Height	6.26 in (15.9 cm)
Net Weight	55.56 lb(US) (25.2 kg)
Width	4.21 in (10.7 cm)

### Conformance

Product certifications	CE
Standards	UL 1778

### Environmental

Ambient air temperature for operation	64...81 °F (18...27 °C)
Operating altitude	0...3333 ft
Relative humidity	0...95 %
Ambient air temperature for storage	32...104 °F (0...40 °C)
Storage altitude	0...15000 ft (0.00...4572.00 m)
Storage Relative Humidity	0...95 %

### Batteries & Runtime

Battery Placement	Internal Battery
Battery blocks per string	8
Battery Slots Empty	0
Included Battery Modules	0
Device mounting	Enclosed battery cartridge
Battery type	VRLA
Battery Volt-Amp-Hour Capacity	864 VAh



Ordering and shipping details

Package weight(Lbs)	59.52 lb(US) (27 kg)
---------------------	----------------------

Packing Units

Package 1 Height	7.09 in (18 cm)
Package 1 width	5.91 in (15 cm)
Package 1 Length	31.89 in (81 cm)
Number of Units in Package 3	32

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SYBTU2-PLPLL](#)