



## Overview

Lead time	Usually Ships within 2 Weeks
-----------	------------------------------

## General

Provided Equipment	Installation guide
--------------------	--------------------

## Physical

Number of rack unit	3U
Color	Black
Depth	27.56 in (70 cm)
Height	5.24 in (13.3 cm)
Net Weight	58.11 lb(US) (26.36 kg)
Width	19.02 in (48.3 cm)

## Input

Input Frequency	60 Hz +/- 3 Hz
Number of input connectors	1 Hard Wire 5-wire (3PH + N + G)
Efficiency at full load	177...239 V 208 V
Nominal Input Voltage	208 V 3 phase

## Output

Kw Rating	10000 W
Max Configurable Power (Watts)	10000 W
Harmonic distortion	Less than 5 % at full load
Output Frequency (sync to mains)	57...63 Hz for 60 Hz nominal sync to mains 60 Hz +/- 0.1 % for 60 Hz nominal not synced
Crest factor	Unlimited
Topology	Double Conversion Online
Waveform Type	Sine wave
Output connector type	Hard Wire 5-wire (3PH + N + G) 1
Output voltage	208 V 208 V 3 phase

## Conformance

Product Certifications	CUL Listed UL Listed
Standards	FCC Part 15 class A ISO 14001 ISO 9001 UL 60950

## Environmental

Ambient air temperature for operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...3333 ft
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Storage Relative Humidity	0...95 %
Acoustic level	64 dBA
Heat dissipation	2970 Btu/h

## Batteries & Runtime

Included Battery Modules	0
Battery Slots Empty	0
Liquid Electrolyte Value	0

## Communications & Management

Free slots	0
Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

## Ordering and shipping details

Package weight(Lbs)	70.15 lb(US) (31.82 kg)
---------------------	-------------------------

## Packing Units

Package 1 Height	10.75 in (27.3 cm)
Package 1 width	22.01 in (55.9 cm)
Package 1 Length	32.76 in (83.2 cm)
Number of Units in Package 3	8

## Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

## Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SYPM10KF](#)