

SYPM2KU

APC Symmetra RM 2-6kVA Power Module (2kVA)



Overview

Presentation	High density, double-conversion on-line power protection with scalable runtime.
Lead time	Usually in Stock

General

Provided Equipment	Installation guide
--------------------	--------------------

Physical

Number of rack unit	0U
Depth	21.50 in (54.61 cm)
Height	3.25 in (8.26 cm)
Product Weight	17.04 lb(US) (7.73 kg)
Width	8.50 in (21.59 cm)

Input

Input Frequency	50/60 Hz +/- 5 Hz auto-sensing
Efficiency at full load	155...276 V
Nominal Input Voltage	200 V 208 V

Output

Kw Rating	1400 W
Max Configurable Power (Watts)	1400 W
Output voltage	200 V 208 V 230 V

Batteries & Runtime

Included Battery Modules	0
Battery Slots Empty	0
Liquid Electrolyte Value	0

Ordering and shipping details

GTIN	00731304016885
Package weight(Lbs)	20.04 lb(US) (9.09 kg)

Packing Units

Package 1 Height	9.75 in (24.77 cm)
Package 1 width	14.00 in (35.56 cm)
Package 1 Length	26.00 in (66.04 cm)

Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
-------------------	---

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SYPM2KU](#)