



### Overview

Presentation	High density, double-conversion on-line power protection with scalable runtime.
Lead time	Usually in Stock

### General

Provided Equipment	Installation guide
--------------------	--------------------

### Physical

Number of rack unit	4U
Depth	22.24 in (56.5 cm)
Height	5.91 in (15 cm)
Product Weight	33.07 lb(US) (15 kg)
Width	9.84 in (25 cm)

### Input

Input Frequency	45...65 Hz auto-sensing
Efficiency at full load	155...276 V 1:1 290...480 V 3:1
Other Input Voltages	220 V 240 V 380 V 415 V
Nominal Input Voltage	230 V 3 phase

### Output

Kw Rating	2800 W
Max Configurable Power (Watts)	2800 W
Output Frequency (sync to mains)	50 Hz +/- 0.1 % for 50 Hz nominal not synced 60 Hz +/- 0.1 % for 60 Hz nominal not synced
Other Output Voltages	220 V 240 V
Crest factor	Up to 5 : 1
Topology	Double Conversion Online
Waveform Type	Sine wave
Output connector type	Hard Wire 3-wire (H N + E) 1
Output voltage	230 V

## Conformance

Product Certifications	C-tick CE GOST VDE
Standards	EN 50091-1 EN 50091-2 EN 55022 Class A EN 55024 EN 60950 IEC 60950

## Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...15000 ft (0.00...4572.00 m)
Acoustic level	62 dBA

## Batteries & Runtime

Included Battery Modules	0
Battery Slots Empty	0
Additional information	Configurable for 220 : 230 or 240 nominal output voltage
Liquid Electrolyte Value	0

## Ordering and shipping details

GTIN	00731304218883
Package weight(Lbs)	40.08 lb(US) (18.18 kg)

## Packing Units

Package 1 Height	17.28 in (43.9 cm)
Package 1 width	12.99 in (33 cm)
Package 1 Length	22.24 in (56.5 cm)
Number of Units in Package 3	6

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SYPM4KI](#)