

Product data sheet

Specifications



Rack PDU, Basic, 1U, 20A, 120V, (10)5-20; L5-20P

AP9564

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Output Voltage	120 V
Main Input Voltage	100 V 120 V
Plug standard	NEMA L5-20P
Number of rack unit	1U
Cable length	12 ft (3.66 m)
Number of cables	1

General

Provided Equipment	Installation guide Rack Mounting brackets
--------------------	--

Physical

Color	Black
Depth	2.24 in (5.7 cm)
Height	1.73 in (4.4 cm)
Net Weight	5.51 lb(US) (2.5 kg)
Width	17.60 in (44.7 cm)

Input

Line Rated Current	16 A
Input current limits	20 A
Load Capacity	1920 VA
Input Frequency	50/60 Hz

Output

Number of power socket outlets	10 NEMA 5-20R
--------------------------------	---------------

Conformance

Product Certifications	cUL Listed UL Listed
------------------------	-------------------------

Environmental

Ambient air temperature for operation	23...113 °F (-5...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	00731304203872
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	No
Country of origin	IN

Packing Units

Package 1 Height	2.76 in (7 cm)
Package 1 width	18.27 in (46.4 cm)
Package 1 Length	9.02 in (22.9 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AP9564](#)