

# Product data sheet

Specifications



Head for non illuminated push button, Harmony XB5, black Ø 30 mushroom pushbutton Ø22 mm spring return sold by 100

ZB5AC24TQ

Product availability : Non-Stock - Not normally stocked in distribution facility

Price\* : 29.40 USD

## Main

|                               |                                      |
|-------------------------------|--------------------------------------|
| Range of Product              | Harmony XB5                          |
| Product or Component Type     | Head for non-illuminated push-button |
| Device short name             | ZB5                                  |
| Bezel material                | Dark grey plastic                    |
| Head type                     | Standard                             |
| Mounting diameter             | 0.87 in (22 mm)                      |
| Sale per indivisible quantity | 100                                  |
| Shape of signaling unit head  | Round                                |
| Type of operator              | spring return                        |
| Operator profile              | Black mushroom Ø 30 mm, unmarked     |

## Complementary

|                             |                                                                                                                                                                                                |
|-----------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| CAD overall width           | 1.18 in (30 mm)                                                                                                                                                                                |
| CAD overall height          | 1.18 in (30 mm)                                                                                                                                                                                |
| CAD overall depth           | 2.05 in (52 mm)                                                                                                                                                                                |
| Net Weight                  | 0.06 lb(US) (0.027 kg)                                                                                                                                                                         |
| Mechanical durability       | 5000000 cycles                                                                                                                                                                                 |
| Station name                | XALD 1...5 cut-outs<br>XALK 2...5 cut-outs                                                                                                                                                     |
| Electrical composition code | C1 9 single front mounting<br>C2 9 single and double front mounting<br>C11 3 single front mounting<br>C15 1 single front mounting<br>SF1 3 single front mounting<br>SR1 3 single rear mounting |
| Compatibility code          | ZB5                                                                                                                                                                                            |

## Environment

|                                     |                            |
|-------------------------------------|----------------------------|
| Protective treatment                | TH                         |
| Ambient Air Temperature for Storage | -40...158 °F (-40...70 °C) |

\* Price is “List Price” and may be subject to a trade discount – check with your local distributor or retailer for actual price.

|                                       |                                                                                                                     |
|---------------------------------------|---------------------------------------------------------------------------------------------------------------------|
| Ambient air temperature for operation | -40...158 °F (-40...70 °C)                                                                                          |
| Overvoltage category                  | Class II IEC 60536                                                                                                  |
| IP degree of protection               | IP66 IEC 60529<br>IP69<br>IP69K                                                                                     |
| NEMA degree of protection             | NEMA 13<br>NEMA 4X                                                                                                  |
| Resistance to high pressure washer    | 1015.26 psi (7000000 Pa) 131 °F (55 °C) 0.1 m                                                                       |
| IK degree of protection               | IK03 IEC 50102                                                                                                      |
| Standards                             | EN/IEC 60947-5-4<br>JIS C8201-5-1<br>CSA C22.2 No 14<br>UL 508<br>EN/IEC 60947-5-1<br>EN/IEC 60947-1<br>JIS C8201-1 |
| Product Certifications                | UL Listed<br>GL<br>DNV<br>CSA<br>LROS (Lloyds register of shipping)<br>BV                                           |
| Vibration resistance                  | 5 gn 2...500 Hz)IEC 60068-2-6                                                                                       |
| Shock resistance                      | 30 gn 18 ms) half sine wave acceleration IEC 60068-2-27<br>50 gn 11 ms) half sine wave acceleration IEC 60068-2-27  |

### Ordering and shipping details

|                       |                                       |
|-----------------------|---------------------------------------|
| Category              | 22467 - PUSHBUTTONS,22MM(PLASTIC) NEW |
| Discount Schedule     | CS2                                   |
| GTIN                  | 3389119077828                         |
| Nbr. of units in pkg. | 1                                     |
| Package weight(Lbs)   | 1.62 oz (46 g)                        |
| Returnability         | No                                    |
| Country of origin     | CZ                                    |

### Packing Units

|                              |                         |
|------------------------------|-------------------------|
| Unit Type of Package 1       | PCE                     |
| Package 1 Height             | 2.05 in (5.2 cm)        |
| Package 1 width              | 1.57 in (4 cm)          |
| Package 1 Length             | 1.57 in (4 cm)          |
| Unit Type of Package 2       | BAG                     |
| Number of Units in Package 2 | 50                      |
| Package 2 Weight             | 5.07 lb(US) (2.3 kg)    |
| Package 2 Height             | 2.05 in (5.2 cm)        |
| Package 2 width              | 1.57 in (4 cm)          |
| Package 2 Length             | 1.57 in (4 cm)          |
| Unit Type of Package 3       | S02                     |
| Number of Units in Package 3 | 100                     |
| Package 3 Weight             | 11.14 lb(US) (5.055 kg) |
| Package 3 Height             | 5.91 in (15 cm)         |

|                  |                  |
|------------------|------------------|
| Package 3 width  | 11.81 in (30 cm) |
| Package 3 Length | 15.75 in (40 cm) |

Offer Sustainability

|                            |                                                                                                                                                                                                                                                                                       |
|----------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                                                 |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                     |
| REACH free of SVHC         | Yes                                                                                                                                                                                                                                                                                   |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>                                                                                                                                                                                     |
| Toxic heavy metal free     | Yes                                                                                                                                                                                                                                                                                   |
| Mercury free               | Yes                                                                                                                                                                                                                                                                                   |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                                                   |
| China RoHS Regulation      | <a href="#">China RoHS declaration</a>                                                                                                                                                                                                                                                |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                         |
| Circularity Profile        | <a href="#">End of Life Information</a>                                                                                                                                                                                                                                               |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ZB5AC24TQ](#)