

# Product datasheet

Specifications



## APC Netshelter SX, Server Rack Enclosure, 48U, Black, 2258H x 600W x 1070D mm

AR3107

### Overview

Presentation	Tall enclosure with 48U spaces for additional equipment. Compact width to optimize data center space. For low to medium density server and networking applications.
Lead time	Usually in Stock

### Main

Number of rack unit	48U
---------------------	-----

### General

Provided equipment	Baying hardware Key(s) Keyed-alike doors and side panels Leveling feet Mounting hardware Pre-installed casters Side panels
--------------------	--

### Physical

Maximum mounting depth	91.49 cm
Minimum mounting depth	19.1 cm
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
Colour	Black
Depth	107 cm
Rack width	19"
Height	225.8 cm
Net weight	138.23 kg
Permanent permissible load	1020.58 kg dynamic 1700.97 kg static
Width	60 cm

### Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Packing Units

Package 1 Weight	157.68 kg
Package 1 Height	238.5 cm
Package 1 width	75.2 cm
Package 1 Length	115.6 cm
Number of Units in Package 3	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AR3107](#)