

Product data sheet

Specifications



Rack PDU,Basic, Zero U,14.4kW,208V,(24)C13,(4)C19,(2)L6-30R;10' Cord

AP7599

Overview

Presentation	Basic Rack PDU 14.4 kW solution for high density installations
Lead time	Usually in Stock

General

Provided Equipment	Cord retention bracket(s) Documentation CD Installation guide Rack Mounting brackets Toolless Mounting Kit
--------------------	--

Physical

Cable length	10 ft (3.05 m)
Color	Black
Depth	3.74 in (9.5 cm)
Height	70.00 in (177.8 cm)
Net Weight	21.74 lb(US) (9.86 kg)
Width	2.20 in (5.6 cm)

Input

Line Rated Current	40 A
Input current limits	50 A
Load Capacity	14400 VA
Input Frequency	50/60 Hz
Number of input connectors	1 CS8365
Nominal Input Voltage	3 phase

Output

Number of power socket outlets	2 NEMA L6-30R 24 IEC 60320 C13 4 IEC 60320 C19
--------------------------------	--

Conformance

Product Certifications	cUL Listed CSA METI Denan
------------------------	---------------------------------

	UL Listed
Standards	UL 60950

Environmental

Ambient air temperature for operation	23...113 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	00731304240761
Package weight(Lbs)	30.47 lb(US) (13.82 kg)

Packing Units

Package 1 Height	80.98 in (205.7 cm)
Package 1 width	3.11 in (7.9 cm)
Package 1 Length	12.24 in (31.1 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AP7599](#)