

Main

| | |
|------------------------------|---|
| Device short name | G |
| Enclosure type | Weatherproof enclosure indoor/outdoor |
| Product Specific Application | Control electrically driven water pumps and air compressors |
| Range of Product | Square D Pumptrol |
| Switch application | Standard |

Complementary

| | |
|-------------------------------------|--|
| Adjustable range on rising pressure | 80...250 psi (551.58...1723.69 kPa) |
| Approximate adjustable differential | 25...45 psi (172.37...310.26 kPa) |
| Depth | 3.68 in (93.47 mm) |
| Electrical connection | Screw clamp terminal |
| Fixing Mode | By brackets |
| Fluid connection type | 0.25 inch NPSF internal |
| Height | 5.72 in (145.29 mm) |
| Material | Zinc plated steel flange |
| Materials in contact with fluid | Nitrile (Buna-N) diaphragm |
| Maximum pressure | 300 psig |
| Maximum Horse Power Rating | 2 Hp 230 V AC, 1 phase 1 Hp 115 V AC, 1 phase 2 hp 460/575 V AC, 1 phase |
| Number of poles | 2 |
| Permissible voltage | 575 V AC |
| Pressure actuator | Diaphragm |
| Pressure setting range | 145...175 psi (999.74...1206.58 kPa) |
| Net Weight | 2.25 lb(US) (1.02 kg) |
| Range on decreasing pressure | 32...215 psi (220.63...1482.37 kPa) |
| Scale type | Adjustable differential |
| Switch function | DPDT |
| Width | 3.44 in (87.38 mm) |

Environment

| | |
|---------------------------|--|
| NEMA degree of protection | NEMA 3R |
| Product Certifications | UL listed file E12158 CCN NKPZ CSA file LR25490 |

Ordering and shipping details

| | |
|-----------------------|---|
| Category | 21536 - 9013 G COMMERCIAL PRESSURE SWITCH |
| Discount Schedule | CP7G |
| GTIN | 785901407744 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 32.00 oz (907.185 g) |

| | |
|-------------------|----|
| Returnability | No |
| Country of origin | MX |

Packing Units

| | |
|------------------------|----------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 10.16 in (25.806 cm) |
| Package 1 width | 4.00 in (10.16 cm) |
| Package 1 Length | 25.81 in (65.548 cm) |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Schneider Electric:

[9013GHB5J63H](#)