



Main

Range	TeSys
Product name	GV2 LE
Product or component type	Mushroom head emergency stop push-button
Device short name	GV2K
Accessory / separate part category	Enclosure accessory

Complementary

Product compatibility	GV2MC LE1GVMEK GV2MP
Type of operator	Latching turn to release
Diameter	1.57 in (40 mm)
Provided equipment	1 IP55 sealing kit
Height	1.89 in (48 mm)
Maximum Width	2.87 in (73 mm)
Net Weight	0.25 lb(US) (0.115 kg)
Color	Red

Environment

IP degree of protection	IP55
-------------------------	------

Ordering and shipping details

Category	22367 - MANUAL STR PROTECTOR - GV2
Discount Schedule	I11
GTIN	00785901105756
Nbr. of units in pkg.	1
Package weight(Lbs)	0.3 lb(US) (0.14 kg)
Returnability	Yes
Country of origin	CZ

Packing Units

Package 1 Height	0.700 dm
Package 1 width	0.900 dm
Package 1 Length	0.900 dm

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GV2K031](#)