

Product data sheet

Characteristics

DF2BN2000

NFC cartridge fuses, Tesys GS, cylindrical 8.5 mm x 31.5 mm, fuse type gG, 400 VAC, 20 A, without striker

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	TeSys fuse-disconnector
Product or component type	Cartridge fuse
Device short name	DF2
System Voltage	400 V AC
[In] rated current	20 A 400 V
Fuse size	8.5 x 31.5 mm
Fuse type	NFC
Quantity per set	Set of 10

Complementary

Fuse curve	GG
Product weight	0.02 lb(US) (0.01 kg)

Ordering and shipping details

Category	22621 - IEC PANEL ACCESSORIES
Discount Schedule	I
GTIN	003389110499469
Nbr. of units in pkg.	10
Package weight(Lbs)	0.01
Returnability	N
Country of origin	FR

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0848 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[DF2BN2000](#)