

## Product data sheet

### Characteristics

# ABFTE20SP300

connection cable - Twido discrete output to  
Telefast - 2 x HE10 - 3 m

Product availability: Non-Stock - Not normally stocked in distribution facility



### Main

Range of product	Twido
Accessory / separate part designation	Discrete output pre-formed cable
Accessory / separate part type	Connecting cable
Accessory / separate part category	Connection accessories
Accessory / separate part destination	Discrete output
Product specific application	For application other than use of Advantys Telefast ABE7 sub-base

### Complementary

Product compatibility	TWDDDO16TK TWDDDO32TK
Cable length	9.84 ft (3 m)
AWG gauge	AWG 28
Cable cross section	0 in <sup>2</sup> (0.08 mm <sup>2</sup> )
Electrical connection	1 connector HE10 20 pin(s) preactuator side 1 connector HE10 20 pin(s) Twido side
Product weight	0.46 lb(US) (0.21 kg)

### Ordering and shipping details

Category	22375 - INTERFACE MODULE(ABA,R,S)
Discount Schedule	CP2
GTIN	003389110393774
Nbr. of units in pkg.	1
Package weight(Lbs)	0.37
Returnability	N
Country of origin	TH

### Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ABFTE20SP300](#)