

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range	TeSys
Product or component type	Contacteur coil
Range compatibility	TeSys CVX contacteur TeSys CRX contacteur
Control circuit type	DC
Coil type	Low consumption
[Uc] control circuit voltage	125 V DC

Complementary

Average resistance	16.3 Ohm at 20 °C
--------------------	-------------------

Ordering and shipping details

Category	18074 - SPARE PARTS DISCOUNT I11
Discount Schedule	I11
GTIN	003389110479515
Nbr. of units in pkg.	1
Package weight(Lbs)	2.6899999999999999
Returnability	N
Country of origin	FR

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0801 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[WB1KB130](#)