

# XAPG19501

Harmony XAP, XB2 SL, Empty control station,  
zinc alloy, grey, 1 cut-out 22mm, 80 x 80 x 77  
mm



## Main

|                               |                                              |
|-------------------------------|----------------------------------------------|
| Range of Product              | Harmony XAP                                  |
| Product or Component Type     | Die-cast empty control station               |
| Device short name             | XAPG                                         |
| Product destination           | For Ø 22 mm control and signalling units     |
| Number of cut-out             | 1 cut-out                                    |
| Colour of base of enclosure   | Grey RAL 7032)                               |
| Colour of cover               | Grey RAL 7032)                               |
| Control station type          | Metal                                        |
| Material                      | Die cast zinc                                |
| Sale per indivisible quantity | 1                                            |
| IP degree of protection       | IP65 IEC 60529<br>IP657 NF C 20-010          |
| Resistance to chemical agents | Special treatment can be obtained on request |

## Complementary

|                           |                                |
|---------------------------|--------------------------------|
| Number of vertical rows   | 1                              |
| Number of horizontal rows | 1                              |
| Cut-out dimensions        | Ø 22 mm                        |
| Cable entry               | Cable gland<br>1 x cable gland |
| Thread type               | 3/4 NPT                        |
| CAD overall width         | 3.15 in (80 mm)                |
| CAD overall height        | 3.15 in (80 mm)                |
| CAD overall depth         | 3.03 in (77 mm)                |
| Net Weight                | 1.62 lb(US) (0.734 kg)         |
| Compatibility code        | XAPG                           |

## Environment

|                                       |                                          |
|---------------------------------------|------------------------------------------|
| Protective treatment                  | TH                                       |
| Ambient Air Temperature for Storage   | -40...158 °F (-40...70 °C)               |
| Ambient Air Temperature for Operation | -13...158 °F (-25...70 °C)               |
| Electrical shock protection class     | Class I IEC 60536<br>Class I NF C 20-030 |
| IK degree of protection               | IK07 EN/IEC 62262                        |

## Ordering and shipping details

|                       |                     |
|-----------------------|---------------------|
| Category              | 22475-WALL STATIONS |
| Discount Schedule     | CS2                 |
| GTIN                  | 3389118381902       |
| Nbr. of units in pkg. | 1                   |
| Package weight(Lbs)   | 26.95 oz (764.0 g)  |
| Returnability         | Yes                 |
| Country of origin     | MA                  |

## Packing Units

|                              |                         |
|------------------------------|-------------------------|
| Unit Type of Package 1       | PCE                     |
| Package 1 Height             | 3.62 in (9.2 cm)        |
| Package 1 width              | 3.39 in (8.6 cm)        |
| Package 1 Length             | 3.46 in (8.8 cm)        |
| Unit Type of Package 2       | S02                     |
| Number of Units in Package 2 | 12                      |
| Package 2 Weight             | 21.53 lb(US) (9.766 kg) |
| Package 2 Height             | 5.91 in (15 cm)         |
| Package 2 width              | 11.81 in (30 cm)        |
| Package 2 Length             | 15.75 in (40 cm)        |

## Offer Sustainability

|                            |                                                                                                                                                                                                                                                                                                                                                                        |
|----------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                                                                                                                                  |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                                                                                                      |
| REACH free of SVHC         | Yes                                                                                                                                                                                                                                                                                                                                                                    |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                                                                                                         |
| Toxic heavy metal free     | Yes                                                                                                                                                                                                                                                                                                                                                                    |
| Mercury free               | Yes                                                                                                                                                                                                                                                                                                                                                                    |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                                                                                                                                    |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                                                                                                                                                                                                                                                                                                 |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                                                                                                          |
| Circularity Profile        | <a href="#">End Of Life Information</a>                                                                                                                                                                                                                                                                                                                                |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XAPG19501](#)