



Main

Product or Component Type	Separate inductive head
Range of Product	Telemecanique Radio frequency identification XG

Complementary

Enclosure Material	Nickel Plated Brass
Fixing Mode	By screws
Detector design	Cylindrical
Diameter	1.18 in (30 mm)
Electrical Connection	Connector
ISO thread	M30
[Sn] nominal sensing distance	0.59 in (15 mm)
Net Weight	0.21 lb(US) (0.095 kg)
Shape of legend	Cylindrical
Tag type	Read/write code
Working sensing distance	0.47 in (12 mm)

Environment

Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)
IP Degree of Protection	IP65
Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)

Ordering and shipping details

Category	22491-SENS,IDENTIFICATION DEVICE (XGK)
Discount Schedule	DS2
GTIN	00785901332961
Package weight(Lbs)	0.29 lb(US) (0.133 kg)
Returnability	No
Country of origin	FR

Packing Units

Package 1 Height	0.450 dm
Package 1 width	0.580 dm
Package 1 Length	0.620 dm

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[XGSP301630](#)