

XVC6B35S

Harmony XVC, Monolithic precabled tower light, plastic, red orange green, Ø60, tube mounting, steady or flashing, buzzer, IP23, 24 V AC/DC



Main

Range of Product	Harmony XVC6
Product or Component Type	Complete pre-wired monolithic tower light
Beacon or indicator bank unit type	3 illuminated units
Sound signalling	Buzzer
Mounting diameter	2.36 in (60 mm)
Component name	XVC
Light source	LED steady or flashing red LED steady or flashing orange LED steady or flashing green
[Us] rated supply voltage	24 V
Supply circuit type	AC/DC
Noise level	70...85 dB continuous or intermittent tone)1 m

Complementary

Material	Polycarbonate illuminated unit ABS (acrylonitrile butadiene-styrene) base unit PBT + ABS (UL94HB) top cover STK (chromium-plated) support tube
Product mounting	On support tube, 22 mm
Cable cross section	0.00 in² (0.33 mm²)
AWG Gauge	AWG 22
Cable length	21.65 in (550 mm)
Marking	CE
[Uimp] rated impulse withstand voltage	0.8 kV
Current Consumption	115 mA
Fundamental frequency	2.23 kHz
Flashing frequency	1 Hz
Net Weight	2.16 lb(US) (0.98 kg)
Height	22.17 in (563.1 mm)

Environment

Standards	EN/IEC 61000-6-3 EN/IEC 61000-6-2 EN/IEC 61000-6-4
Product Certifications	UL
Protective treatment	TC
Ambient Air Temperature for Storage	-31...158 °F (-35...70 °C)
Ambient Air Temperature for Operation	14...122 °F (-10...50 °C)
Electrical shock protection class	Class I EN/IEC 61140
IP degree of protection	IP23 vertical surface installation EN/IEC 60529

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	22617-XVC TOWER LIGHTS
Discount Schedule	XV
GTIN	3606480032660
Nbr. of units in pkg.	1
Package weight(Lbs)	2.56 lb(US) (1.162 kg)
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.35 in (8.5 cm)
Package 1 width	3.35 in (8.5 cm)
Package 1 Length	30.31 in (77 cm)
Unit Type of Package 2	S06
Number of Units in Package 2	1
Package 2 Weight	28.66 lb(US) (13.0 kg)
Package 2 Height	28.94 in (73.5 cm)
Package 2 width	23.62 in (60 cm)
Package 2 Length	31.50 in (80 cm)
Unit Type of Package 3	P06
Number of Units in Package 3	20
Package 3 Weight	76.10 lb(US) (34.52 kg)
Package 3 Height	30.31 in (77 cm)
Package 3 width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information


Contractual warranty

Warranty	18 months
----------	-----------

Pre-assembled and Pre-wired Tower Light with Support Tube Mounting

Dimensions


Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get b1 dimension.



No. of illuminated units	b1 With buzzer (mm)	b1 With buzzer (in.)
1 stage	483.1	19.02
2 stages	523.1	20.59
3 stages	563.1	22.17
4 stages	603.1	23.74
5 stages	643.1	25.32

Pre-assembled and Pre-wired Tower Light

Support Tube Mounting



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XVC6B35S](#)