



## Commercial status

This Product is Obsolete : JAN 04, 2022

⚠ This Product is Obsolete

## Overview

|           |                  |
|-----------|------------------|
| Lead time | Usually in Stock |
|-----------|------------------|

## Main

|                       |  |
|-----------------------|--|
| Nominal Input Voltage | 120 V                                  |
| Plug standard         | NEMA 5-15P                             |
| Cable length          | 6 Ft (1.83 m)                          |
| Number of cables      | 1                                      |
| Provided equipment    | 2 x 1.8 Meter Tel cable<br>User Manual |

## Physical

|                     |                       |
|---------------------|-----------------------|
| Color               | Beige                 |
| Height              | 1.73 In (4.4 cm)      |
| Width               | 7.99 In (20.3 cm)     |
| Depth               | 5.75 In (14.6 cm)     |
| Net Weight          | 2.34 Lb(US) (1.06 kg) |
| Mounting preference | No preference         |
| Mounting Mode       | Not rack-mountable    |

## Input

|                 |                                |
|-----------------|--------------------------------|
| Input Frequency | 50/60 Hz +/- 5 Hz auto-sensing |
|-----------------|--------------------------------|

## Output

|                                |            |
|--------------------------------|------------|
| Number of power socket outlets | 8          |
| Outlet standard                | NEMA 5-15R |

## Conformance

|                             |  |
|-----------------------------|--|
| UL 1449 TVSS Rating         | 330                                      |
| Product certifications      | CSA                                      |
| Standards                   | UL 497B<br>UL 1283<br>UL 1363<br>UL 1449 |
| Equipment protection policy | Lifetime : \$75000                       |

## Environmental

|                                       |                                  |
|---------------------------------------|----------------------------------|
| Ambient Air Temperature for Operation | 32...113 °F (0...45 °C)          |
| Relative Humidity                     | 0...95 %                         |
| Operating altitude                    | 0...10000 ft                     |
| Ambient Air Temperature for Storage   | 5...113 °F (-15...45 °C)         |
| Storage Relative Humidity             | 0...95 %                         |
| Storage altitude                      | 0...50000 Ft (0.00...15240.00 m) |

## Surge Protection and Filtering

|   |   |
|---|---|
| EP Joule Rating                           | 1760 J  |
| Data Lines Protected<br>(multi-line only) | 1-4   |
| NM Surge Response Time (ns)               | 0 ns common mode                                    |
| Common mode rejection                     | 60 DB   |
| Peak current                              | 13 KA common mode<br>13 KA normal mode              |
| Surge energy rating                       | 1120 J  |
| Data line protection                      | RJ11 Modem/Fax/DSL protection (four wire dual line) |

## Ordering and shipping details

|                     |                       |
|---------------------|-----------------------|
| GTIN                | 00731304400820        |
| Package weight(Lbs) | 2.51 Lb(US) (1.14 kg) |

## Packing Units

|                              |                        |
|------------------------------|------------------------|
| Package 1 Height             | 2.01 In (5.1 cm)       |
| Package 1 width              | 12.52 In (31.8 cm)     |
| Package 1 Length             | 6.26 In (15.9 cm)      |
| SCC14                        | 10731304000836         |
| Number of Units in Package 2 | 12                     |
| Package 2 Weight             | 31.9 Lb(US) (14.47 kg) |
| Number of Units in Package 3 | 240                    |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product                         |
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>                           |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |
| Circularity Profile        | <a href="#">End Of Life Information</a>       |

Contractual warranty

|          |                  |
|----------|------------------|
| Warranty | Limited Lifetime |
|----------|------------------|

|                       |                        |
|-----------------------|------------------------|
| Product Life Status : | Post commercialisation |
|-----------------------|------------------------|

PRO8T2 may be replaced by any of the following products:



P8T3  
APC Home Office SurgeArrest 8 Outlet with Phone (Splitter) Protection, 120V  
Qty 1  
Substitution date: |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[PRO8T2](#)