

SMT3000R2X180

APC Smart-UPS, Line Interactive, 3kVA,
Rackmount 2U, 120V, 6x NEMA 5-15R+2x
NEMA 5-20R outlets, SmartSlot, AVR, LCD



Commercial status

End-of-Sale Notice : SEP 30, 2021

⚠ End-of-Sale Notice

Overview

Lead time	Usually Ships within 3 Weeks
-----------	------------------------------

Main

Input voltage	120 V
Output voltage	120 V
Rated power in W	2700 W
Rated power in VA	2880 VA
Plug standard	NEMA L5-30P
Nb of power socket outlets	6 NEMA 5-15R 2 NEMA 5-20R
Number of rack unit	2U
Cable length	2.44 M
Number of cables	1
Battery type	Lead-acid battery
Provided equipment	CD with software Documentation CD Installation guide Rack mounting hardware Rack mounting support rails Smart UPS signalling RS-232 cable USB cable Web/SNMP management card

General

Number of power module filled slots	0
Number of power module free slots	0
Redundant	No
Variant option	Web/SNMP card AP9630 preinstalled

Physical

Colour	Black
Height	8.6 Cm
Width	48 Cm
Depth	68.3 Cm
Net weight	44.28 Kg
Mounting location	Front
Mounting preference	Lower
Mounting mode	Rack-mounted
Two post mountable	0
USB compatible	Yes

Input

Input voltage limits	75...154 V adjustable 82...144 V
Network frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic distortion	Less than 5 %
Maximum configurable power in VA	2880 VA
Maximum configurable power in W	2700 W
Transfer time	4 ms typical : 8 ms maximum
UPS type	Line interactive
Wave type	Sine wave
Output frequency	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product certifications	CSA
Equipment protection policy	Lifetime : \$150000
Standards	FCC part 15 class A UL 1778

Environmental

Acoustic level	55 dBA
Heat dissipation	348 Btu/H
Operating altitude	0...10000 ft
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 M
Relative humidity	0...95 %
Storage Relative Humidity	0...95 %

Batteries & Runtime

Extended runtime	0
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 H
Number of battery replacement quantity	1
Battery life	3...5 Year(S)
Battery power in VAH	566 VAh runtime
Battery charger power	188 W rated

Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous-tone alarm
Control panel	LED status display with on line : on battery : replace battery and overload indicators Multifunction LCD status and control console
Free slots	0
Preinstalled device	Network management card

Surge Protection and Filtering

Surge energy rate	459 J
-------------------	-------

Packing Units

Package 1 Weight	51.7 Kg
Package 1 Height	25.4 Cm
Package 1 width	60 Cm
Package 1 Length	98 Cm
Number of Units in Package 3	8

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and-lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---

Product Life Status : **End of commercialisation**

SMT3000R2X180 may be replaced by any of the following products:



SMT3000RM2U

APC Smart-UPS, Line Interactive, 3kVA, Rackmount 2U, 120V, 6x NEMA 5-15R+2x NEMA 5-20R outlets, SmartSlot.

Qty 1

Substitution date: | Substitution

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SMT3000R2X180](#)