



Main

Accessory / separate part category	Cabling accessory
Accessory / separate part type	Jumper cable

Complementary

Jumper cable end 1	M12 male 4 pins straight connector with screw-on
Jumper cable end 2	M12 female 4 pins straight connector with screw-on
Collar material	Metal
Cable composition	4 x 0.34 mm ²
Cable length	2 M
Wire insulation material	PUR (shielded cable)
Cable outer diameter	5.9 Mm
[Ue] rated operational voltage	250 V AC 300 V DC
[In] rated current	4 A
Insulation resistance	>= 1000 MOhm
Maximum resistance across terminals	5000 MOhm
Net weight	0.3 Kg

Environment

IP degree of protection	IP65 IP67
Ambient air temperature for operation	-25...80 °C static
Ambient air temperature for storage	-25...80 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	125.0 G
Package 1 Height	2.0 Cm
Package 1 width	16.5 Cm
Package 1 Length	18.0 Cm
Unit Type of Package 2	S02
Number of Units in Package 2	40
Package 2 Weight	5.358 Kg
Package 2 Height	15.0 Cm
Package 2 width	30.0 Cm
Package 2 Length	40.0 Cm

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and-Di-isodecyl phthalate (DIDP), which is known to the State of California to-cause birth defects or other reproductive harm. For more information go-to www.P65Warnings.ca.gov

Product Life Status :	Commercialised
-----------------------	----------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XZCRB151141C2](#)