

## Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--



## Main

Main Input Voltage	3 phase 3 phase 3 phase 3 phase
--------------------	--

## General

Air Discharge Patterns	Horizontal Upflow
Air flow	16672 ft³/min (7868.31 l/s)
Inrush current	10 A

## Physical

Height	32.44 in (82.4 cm)
Width	38.46 in (97.7 cm)
Depth	124.06 in (315.1 cm)
Net Weight	479.99 lb(US) (217.72 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Length	10.34 ft (3.15 m)

## Input

Minimum Circuit Amp Capacity	12 A
Input Frequency	60 Hz
Maximum Overcurrent Protection	15 A

## Conformance

Product Certifications	ETL
------------------------	-----

## Environmental

Ambient Air Temperature for Operation	-4...122 °F (-20...50 °C)
Operating altitude	0...10000 ft
Audible noise at 1 meter from surface of unit	65 dBA

## Ordering and shipping details

GTIN	731304327882
Package weight(Lbs)	600.01 lb(US) (272.16 kg)

## Packing Units

Package 1 Height	35.00 in (88.9 cm)
Package 1 width	42.99 in (109.2 cm)
Package 1 Length	130.00 in (330.2 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Lead free	Yes

## Contractual warranty

Warranty	1 year (parts only)
----------	---------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ACCD75228](#)