



Main

Product or Component Type	Cover
Accessory / separate part category	Cabling accessories
Range compatibility	Spacial (S3D) Spacial (CRN) Thalassa PLA Thalassa PLS Thalassa PLM
Mounting support	Cable duct 0.98 in (25 mm)
Quantity per Set	Set of 8

Complementary

Color	Gray RAL 7030)
Length	78.74 in (2000 mm)
Width	0.98 in (25 mm)
Material	PVC (polyvinyl chloride)
Net Weight	0.35 lb(US) (0.16 kg)

Environment

Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Flame retardance	V-0 UL 94
Fire resistance	1760 °F (960 °C) IEC 60695-2-1/1
Standards	DIN 43659 VDE 0506 VDE 0660

Ordering and shipping details

Category	22622-PANEL BUS_(OLD STYLE)
Discount Schedule	I
GTIN	3389110570502
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.39 in (1.000 cm)
Package 1 Width	0.98 in (2.500 cm)
Package 1 Length	78.94 in (200.500 cm)
Package 1 Weight	5.54 oz (157.000 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	1.18 in (3.000 cm)
Package 2 Width	1.57 in (4.000 cm)
Package 2 Length	79.53 in (202.000 cm)
Package 2 Weight	3.40 lb(US) (1.544 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AK2CD25](#)